



**HEADER STRAIGHT SOLDER PIN, 1X1  
MM / 0.039X 0.039 IN PIN SPACING 7.5  
MM / 0.295 IN 100% PROTECTED  
AGAINST MISMATING  
721-232/001-000 TO 721-242/001-000**

<b>ITEM-NO. (ITEM-NO.)</b>	721-240/001-000
<b>Measured voltage (Measured voltage / V)</b>	630
<b>Measured shock voltage (Measured shock voltage / kV)</b>	6
<b>Pollution degree (Pollution degree)</b>	2
<b>Current intensity (Current intensity / A)</b>	12
<b>RM (PIN SPACING / mm)</b>	7.5
<b>P (NO. OF POLES)</b>	10
<b>Height (Height / mm)</b>	12
<b>Width (Width / mm)</b>	75.5
<b>Depth (Depth / mm)</b>	11.4
<b>COLOR (COLOR)</b>	lichtgrau
<b>WEIGHT (WEIGHT / g)</b>	4.13
<b>Comment (Comment)</b>	A = (No. of poles - 1) x Pin Spacing + 8,2 mm
<b>Dimensions (Dimensions)</b>	1,4 +0,1 mm