



**HEADER STRAIGHT SOLDER PIN, 1.2
X 1.2 MM / 0.047 X 0.047 IN PIN
SPACING 7.5 MM / 0.295 IN 100%
PROTECTED AGAINST MISMATING
721-262/001-000 TO 721-272/001-000**

| | |
|---|---|
| ITEM-NO. (ITEM-NO.) | 721-262/001-000 |
| Measured voltage (Measured voltage / V) | 630 |
| Measured shock voltage (Measured shock voltage / kV) | 6 |
| Pollution degree (Pollution degree) | 2 |
| Current intensity (Current intensity / A) | 16 |
| RM (PIN SPACING / mm) | 7.5 |
| P (NO. OF POLES) | 2 |
| Height (Height / mm) | 12 |
| Width (Width / mm) | 15.5 |
| Depth (Depth / mm) | 11.4 |
| COLOR (COLOR) | lichtgrau |
| WEIGHT (WEIGHT / g) | 1.054 |
| Comment (Comment) | A = (No. of poles - 1) x Pin Spacing + 8,2 mm |
| Dimensions (Dimensions) | 1,7 +0,1 mm |