



**HEADER STRAIGHT SOLDER PIN, 1.2
X 1.2 MM / 0.047 X 0.047 IN PIN
SPACING 7.5 MM / 0.295 IN 100%
PROTECTED AGAINST MISMATING
721-262/001-000 TO 721-272/001-000**

ITEM-NO. (ITEM-NO.)	721-265/001-000
Measured voltage (Measured voltage / V)	630
Measured shock voltage (Measured shock voltage / kV)	6
Pollution degree (Pollution degree)	2
Current intensity (Current intensity / A)	16
RM (PIN SPACING / mm)	7.5
P (NO. OF POLES)	5
Height (Height / mm)	12
Width (Width / mm)	38
Depth (Depth / mm)	11.4
COLOR (COLOR)	lichtgrau
WEIGHT (WEIGHT / g)	2.53
Comment (Comment)	A = (No. of poles - 1) x Pin Spacing + 8,2 mm
Dimensions (Dimensions)	1,7 +0,1 mm