



**ANGLED FEMALE PLUG WITH SNAP-  
IN MOUNTING FOOT PIN SPACING 7.5  
MM / 0.295 IN 100% PROTECTED  
AGAINST MISMATING**  
721-332/008-000 TO 721-342/008-000

<b>ITEM-NO. (ITEM-NO.)</b>	721-339/008-000
<b>Cross section1 (Cross section / mm<sup>2</sup>)</b>	0.08 - 2.5
<b>Cross section2 (Cross section / AWG)</b>	28 - 12
<b>Strip length (Strip length / mm)</b>	8 - 9
<b>Measured voltage (Measured voltage / V)</b>	630
<b>Measured shock voltage (Measured shock voltage / kV)</b>	6
<b>Pollution degree (Pollution degree)</b>	2
<b>Current intensity (Current intensity / A)</b>	12
<b>RM (PIN SPACING / mm)</b>	7.5
<b>P (NO. OF POLES)</b>	9
<b>Height (Height / mm)</b>	13.1
<b>Width (Width / mm)</b>	66.5
<b>Depth (Depth / mm)</b>	23
<b>No. of connection Points (No. of connection Points)</b>	9
<b>No. of potentials (No. of potentials)</b>	9
<b>COLOR (COLOR)</b>	lichtgrau
<b>WEIGHT (WEIGHT / g)</b>	
<b>Comment (Comment)</b>	$L = (\text{No. of poles} - 1) \times \text{Pin Spacing} + 5 \text{ mm} + 1,5 \text{ mm}$