



**ANGLED FEMALE PLUG WITH FIXING
FLANGE PIN SPACING 7.5 MM / 0.295
IN 100% PROTECTED AGAINST
MISMATING**

721-332/031-000 TO 721-342/031-000

| | |
|--|--|
| ITEM-NO. (ITEM-NO.) | 721-342/031-000 |
| Cross section1 (Cross section / mm ²) | 0.08 - 2.5 |
| Cross section2 (Cross section / AWG) | 28 - 12 |
| Strip length (Strip length / mm) | 8 - 9 |
| Measured voltage (Measured voltage / V) | 630 |
| Measured shock voltage (Measured shock voltage / kV) | 6 |
| Pollution degree (Pollution degree) | 2 |
| Current intensity (Current intensity / A) | 12 |
| RM (PIN SPACING / mm) | 7.5 |
| P (NO. OF POLES) | 12 |
| Height (Height / mm) | 13.1 |
| Width (Width / mm) | 102.3 |
| Depth (Depth / mm) | 23 |
| No. of connection Points (No. of connection Points) | 12 |
| No. of potentials (No. of potentials) | 12 |
| COLOR (COLOR) | lichtgrau |
| WEIGHT (WEIGHT / g) | |
| Comment (Comment) | L1 = (No. of poles - 1) x Pin Spacing + 5 mm + 3 mm L2 = (No. of poles - 1) x Pin Spacing + 5 mm + 8,8 mm L3 = (No. of poles - 1) x Pin Spacing + 5 mm + 14,8 mm |