



**HEADER RIGHT ANGLE SOLDER PIN,
1 X 1 MM / 0.039 X 0.039 IN PIN
SPACING 5 MM / 0.197 IN 100%
PROTECTED AGAINST MISMATING
WITH PRECEDING EARTH
721-433/001-040 TO 721-435/001-040**

ITEM-NO. (ITEM-NO.)	721-435/001-040
Measured voltage (Measured voltage / V)	320
Measured shock voltage (Measured shock voltage / kV)	4
Pollution degree (Pollution degree)	2
Current intensity (Current intensity / A)	12
RM (PIN SPACING / mm)	5
P (NO. OF POLES)	5
Height (Height / mm)	11.4
Width (Width / mm)	28.2
Depth (Depth / mm)	12
COLOR (COLOR)	lichtgrau
WEIGHT (WEIGHT / g)	1.874
Comment (Comment)	A = (No. of poles x Pin Spacing) + 3,2 mm B = A + 5 mm C = B + 7,4 mm
Dimensions (Dimensions)	1,4 +0,1 mm