



**MALE CONNECTOR WITH SNAP-IN
MOUNTING FOOT PIN SPACING 5 MM
/ 0.197 IN 100% PROTECTED AGAINST
MISMATING**

721-602/018-000 TO 721-620/018-000

ITEM-NO. (ITEM-NO.)	721-607/018-000
Cross section1 (Cross section / mm ²)	0.08 - 2.5
Cross section2 (Cross section / AWG)	28 - 12
Strip length (Strip length / mm)	8 - 9
Measured voltage (Measured voltage / V)	320
Measured shock voltage (Measured shock voltage / kV)	4
Pollution degree (Pollution degree)	2
Current intensity (Current intensity / A)	12
RM (PIN SPACING / mm)	5
P (NO. OF POLES)	7
Height (Height / mm)	14.3
Width (Width / mm)	38.2
Depth (Depth / mm)	27.5
No. of connection Points (No. of connection Points)	7
No. of potentials (No. of potentials)	7
COLOR (COLOR)	lichtgrau
Comment (Comment)	A = (No. of poles x Pin Spacing) + 3,2 mm B = A - 1,7 mm C = A - 1,2 mm