



**MALE CONNECTOR WITH FIXING
FLANGE PIN SPACING 5 MM / 0.197 IN
100% PROTECTED AGAINST
MISMATING**

721-602/019-000 TO 721-620/019-000

ITEM-NO. (ITEM-NO.)	721-610/019-000
Cross section1 (Cross section / mm²)	0.08 - 2.5
Cross section2 (Cross section / AWG)	28 - 12
Strip length (Strip length / mm)	8 - 9
Measured voltage (Measured voltage / V)	320
Measured shock voltage (Measured shock voltage / kV)	4
Pollution degree (Pollution degree)	2
Current intensity (Current intensity / A)	12
RM (PIN SPACING / mm)	5
P (NO. OF POLES)	10
Height (Height / mm)	14.3
Width (Width / mm)	64.8
Depth (Depth / mm)	27.5
No. of connection Points (No. of connection Points)	10
No. of potentials (No. of potentials)	10
COLOR (COLOR)	lichtgrau
WEIGHT (WEIGHT / g)	16.41
Comment (Comment)	A = (No. of poles x Pin Spacing) + 3,2 mm D = A - 0,2 mm E = D + 5,8 mm F = D + 11,8 mm