



**HEADER RIGHT ANGLE SOLDER PIN,  
1 X 1 MM / 0.039 X 0.039 IN PIN  
SPACING 7.5 MM / 0.295 IN 100%  
PROTECTED AGAINST MISMATING  
721-832/001-000 TO 721-842/001-000**

|   |  |
|---|--|
| <b>ITEM-NO. (ITEM-NO.)</b>                                  | 721-841/001-000  |
| <b>Measured voltage (Measured voltage / V)</b>              | 630  |
| <b>Measured shock voltage (Measured shock voltage / kV)</b> | 6  |
| <b>Pollution degree (Pollution degree)</b>                  | 2  |
| <b>Current intensity (Current intensity / A)</b>            | 12   |
| <b>RM (PIN SPACING / mm)</b>                                | 7.5  |
| <b>P (NO. OF POLES)</b>                                     | 11   |
| <b>Height (Height / mm)</b>                                 | 11.4   |
| <b>Width (Width / mm)</b>                                   | 83   |
| <b>Depth (Depth / mm)</b>                                   | 12   |
| <b>COLOR (COLOR)</b>  | lichtgrau  |
| <b>WEIGHT (WEIGHT / g)</b>                                  | 4.5  |
| <b>Comment (Comment)</b>                                    | A = (No. of poles - 1) x Pin Spacing + 8,2 mm<br>  B = A + 5 mm   C = B + 7,4 mm |
| <b>Dimensions (Dimensions)</b>                              | 1,4 +0,1 mm  |