



**HEADER RIGHT ANGLE SOLDER PIN,
1.2 X 1.2 MM/ 0.047 X 0.047 IN PIN
SPACING 7.5 MM / 0.295 IN 100%
PROTECTED AGAINST MISMATING
721-862/001-000 TO 721-872/001-000**

ITEM-NO. (ITEM-NO.)	721-871/001-000
Measured voltage (Measured voltage / V)	630
Measured shock voltage (Measured shock voltage / kV)	6
Pollution degree (Pollution degree)	2
Current intensity (Current intensity / A)	16
RM (PIN SPACING / mm)	7.5
P (NO. OF POLES)	11
Height (Height / mm)	11.4
Width (Width / mm)	83
Depth (Depth / mm)	12
COLOR (COLOR)	lichtgrau
WEIGHT (WEIGHT / g)	5.258
Comment (Comment)	A = (No. of poles - 1) x Pin Spacing + 8,2 mm B = A + 5 mm C = B + 7,4 mm
Dimensions (Dimensions)	1,7 +0,1 mm