



**FEMALE PLUG WITH RIGHT ANGLE
LONG CONTACT PINS PIN SPACING 5
MM / 0.197 IN 100% PROTECTED
AGAINST MISMATING**

722-232/005-000 TO 722-250/005-000

ITEM-NO. (ITEM-NO.)	722-234/005-000
Measured voltage (Measured voltage / V)	320
Measured shock voltage (Measured shock voltage / kV)	4
Pollution degree (Pollution degree)	3
Current intensity (Current intensity / A)	12
RM (PIN SPACING / mm)	5
P (NO. OF POLES)	4
Height (Height / mm)	11.6
Width (Width / mm)	21.5
Depth (Depth / mm)	18.25
COLOR (COLOR)	lichtgrau
Comment (Comment)	L = (No. of poles x Pin Spacing) + 1,5 mm