



**FEMALE PLUG WITH FIXING
FLANGES FOR
FEEDTHROUGHAPPLICATIONS PIN
SPACING 5 MM / 0.197 IN 100%
PROTECTED AGAINST MISMATING
WITH RIGHT ANGLED SOLDER PIN
722-232/031-000 TO 722-250/031-000**

| | |
|---|--|
| ITEM-NO. (ITEM-NO.) | 722-235/031-000 |
| Measured voltage (Measured voltage / V) | 320 |
| Measured shock voltage (Measured shock voltage / kV) | 4 |
| Pollution degree (Pollution degree) | 2 |
| Current intensity (Current intensity / A) | 12 |
| RM (PIN SPACING / mm) | 5 |
| P (NO. OF POLES) | 5 |
| Height (Height / mm) | 11.6 |
| Width (Width / mm) | 39.8 |
| Depth (Depth / mm) | 18.25 |
| COLOR (COLOR) | lichtgrau |
| Comment (Comment) | L = (No. of poles x Pin Spacing) + 1,5 mm L1 = L + 3 mm L2 = L + 8,8 mm / L3 = L + 14,8 mm |
| Dimensions (Dimensions) | 1.3 +0.1 mm |