



**FEMALE PLUG WITH LOCKING
LEVER PIN SPACING 5 MM / 0.197 IN
100% PROTECTED AGAINST
MISMATING WITH RIGHT ANGLED
SOLDER PIN**
722-232/039-000 TO 722-250/039-000

ITEM-NO. (ITEM-NO.)	722-236/039-000
Measured voltage (Measured voltage / V)	320
Measured shock voltage (Measured shock voltage / kV)	4
Pollution degree (Pollution degree)	2
Current intensity (Current intensity / A)	12
RM (PIN SPACING / mm)	5
P (NO. OF POLES)	6
Height (Height / mm)	11.6
Width (Width / mm)	45.8
Depth (Depth / mm)	18.25
COLOR (COLOR)	lichtgrau
Comment (Comment)	L = (No. of poles x Pin Spacing) + 1,5 mm
Dimensions (Dimensions)	1.3 +0.1 mm