



**FEMALE PLUG WITH FIXING  
FLANGES FOR  
FEEDTHROUGHAPPLICATIONS PIN  
SPACING 5 MM / 0.197 IN 100%  
PROTECTED AGAINST MISMATING  
WITH RIGHT ANGLED SOLDER PIN  
722-232/031-000 TO 722-250/031-000**

<b>ITEM-NO. (ITEM-NO.)</b>	722-237/031-000
<b>Measured voltage (Measured voltage / V)</b>	320
<b>Measured shock voltage (Measured shock voltage / kV)</b>	4
<b>Pollution degree (Pollution degree)</b>	2
<b>Current intensity (Current intensity / A)</b>	12
<b>RM (PIN SPACING / mm)</b>	5
<b>P (NO. OF POLES)</b>	7
<b>Height (Height / mm)</b>	11.6
<b>Width (Width / mm)</b>	49.8
<b>Depth (Depth / mm)</b>	18.25
<b>COLOR (COLOR)</b>	lichtgrau
<b>Comment (Comment)</b>	L = (No. of poles x Pin Spacing) + 1,5 mm   L1 = L + 3 mm   L2 = L + 8,8 mm / L3 = L + 14,8 mm
<b>Dimensions (Dimensions)</b>	1.3 +0.1 mm