



**FEMALE PLUG WITH LOCKING  
LEVER PIN SPACING 7.5 MM / 0.295 IN  
100% PROTECTED AGAINST  
MISMATING WITH RIGHT ANGLED  
SOLDER PIN  
722-832/039-000 TO 722-842/039-000**

|   |   |
|---|---|
| <b>ITEM-NO. (ITEM-NO.)</b>                                  | 722-832/039-000                             |
| <b>Measured voltage (Measured voltage / V)</b>              | 630   |
| <b>Measured shock voltage (Measured shock voltage / kV)</b> | 6   |
| <b>Pollution degree (Pollution degree)</b>                  | 2   |
| <b>Current intensity (Current intensity / A)</b>            | 12  |
| <b>RM (PIN SPACING / mm)</b>                                | 7.5   |
| <b>P (NO. OF POLES)</b>                                     | 2   |
| <b>Height (Height / mm)</b>                                 | 11.6  |
| <b>Width (Width / mm)</b>                                   | 28  |
| <b>Depth (Depth / mm)</b>                                   | 18.25                                       |
| <b>COLOR (COLOR)</b>  | lichtgrau                                   |
| <b>Comment (Comment)</b>                                    | L = (No. of poles - 1) x Pin Spacing + 5 mm |
| <b>Dimensions (Dimensions)</b>                              | 1.3 +0.1 mm                                 |