



**FEMALE PLUG WITH RIGHT ANGLED
SOLDER PIN PIN SPACING 7.5 MM / 0.
295 IN 100% PROTECTED AGAINST
MISMATING**

722-832 TO 722-842

| | |
|---|---|
| ITEM-NO. (ITEM-NO.) | 722-836 |
| Measured voltage (Measured voltage / V) | 630 |
| Measured shock voltage (Measured shock voltage / kV) | 6 |
| Pollution degree (Pollution degree) | 2 |
| Current intensity (Current intensity / A) | 12 |
| RM (PIN SPACING / mm) | 7.5 |
| P (NO. OF POLES) | 6 |
| Height (Height / mm) | 11.6 |
| Width (Width / mm) | 44 |
| Depth (Depth / mm) | 18.25 |
| COLOR (COLOR) | lichtgrau |
| WEIGHT (WEIGHT / g) | 6.67 |
| Comment (Comment) | L = (No. of poles - 1) x Pin Spacing + 5 mm + 1,5 mm |
| Dimensions (Dimensions) | 1.3 +0.1 mm |