


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

NO WARRANTY, EXPRESSED OR IMPLIED, IS MADE BY PANDUIT WITH RESPECT TO ADHESIVE BOND PERFORMANCE, AMONG OTHER THINGS, THE CONDITIONS UNDER WHICH THESE MOUNTS MAY BE APPLIED AND/OR THE SURFACE TO WHICH THEY MAY BE APPLIED ARE BEYOND PANDUIT'S CONTROL.





ACTUAL SIZE



MAX. BUNDLE DIA. 0.25 [6.4]

* PANDUIT PART NO.	WEIGHT LBS/100 PCS. (g)
VCC25	0.20 (91)



ADHESIVE TAPE: PRESSURE SENSITIVE FOAM 0.040 (1.02) THICK WITH ACRYLIC ADHESIVE AND PROTECTIVE LINER. MOUNT IS DESIGNED TO SUPPORT .25 lbs. (113g) MAXIMUM WEIGHT ON A CLEAN, DRY, SMOOTH, GREASE-FREE SURFACE.

TO APPLY CLIP:

1. REMOVE PROTECTIVE LINER.
2. PLACE IN DESIRED LOCATION.
3. APPLY PRESSURE TO CLIP.

NOTES:

- *1. SEE CURRENT PRICE SHEET FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE.

(DIMENSIONS IN BRACKETS ARE IN METRIC.)

CAD FILENAME/LAYERS GB0146BA_PB_VCC25_A_02

PANDUIT CORP. TINLEY PARK, ILLINOIS

VCC25 - A
VERTICAL CORD CLIP

UNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE:
(.X) ±0.1(2.5) (.XXX) ±0.020(.5)
(.XX) ±0.05(1.3) ANGLES ±5°

UNLESS OTHERWISE SPECIFIED,
ALL DIMENSIONS ARE GIVEN
IN INCHES, THIRD ANGLE PROJECTION.

REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP
2	06/18/01	LGG		UPDATED FOR WEB	GB0146BA	2		
1	12-15-93	STR		DIMENSIONS ADDED	GB0146BA	1		
R	1-23-93	MJK		INITIAL RELEASE	GB0146BA	R		

DRAWN BY MJK
DATE 1-23-93
CHK'D

MAT'L: NATURAL NYLON

SCALE 1.5X
DRAWING NO. GB0146BA
DWG SIZE A