

tesa® extra Power Perfect



56339 / 56341 / 56342 / 56343 / 56344

Product Information

tesa® extra Power Perfect is a powerful high quality acrylic coated cloth tape. It is based on a 145 mesh woven rayon fabric backing and a natural rubber adhesive. It has a high adhesion even on rough surfaces and an excellent tensile strength.

Main Application

- For all professional solutions like handicrafts, fastening, bundling, strengthening and marking
- For permanently high resilience and long-term results
- Very strong and perfect adhesive power, also on rough surfaces
- Tear-resistant but tearable by hand
- Can be written on
- Straight tear edges longitudinal and horizontal
- Wide range of colors
- Formable

Technical information (average values)

The values in this section should be considered as average figures or typical only and should not be used for specification purposes.

Technical Data

• Backing material	Acrylic-coated cloth	• Elongation at break	13%
• Total thickness	310 µm	• Tensile strength	100 N/cm
• Type of adhesive	Natural rubber	• Mesh	145 count per m ²
		• Temperature resistance (30min)	130 °C

Adhesion to

- | | |
|---------|----------|
| • steel | 3.3 N/cm |
|---------|----------|

Properties

- | | | | |
|----------------------------|------|-----------------------|------|
| • Hand tearability | ●●●● | • Abrasion resistance | ●●●● |
| • Straight tear edges | ●●●● | • Water resistance | ●●● |
| • Suitable for die cutting | yes | | |

Evaluation across relevant tesa® assortment: ●●●● very good ●●● good ●● medium ● low

