



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

NO WARRANTY, EXPRESSED OR IMPLIED, IS MADE BY PANDUIT WITH RESPECT TO ADHESIVE BOND PERFORMANCE. AMONG OTHER THINGS, THE CONDITIONS UNDER WHICH THESE MOUNTS MAY BE APPLIED, AND/OR THE SURFACE TO WHICH THEY MAY BE APPLIED, ARE BEYOND PANDUIT'S CONTROL.



ADHESIVE BACKING:
 PRESSURE SENSITIVE FOAM TAPE, .04(1.0) THICK,
 WITH RUBBER (-A) OR ACRYLIC (-AT) ADHESIVE
 AND PROTECTIVE LINER. LINER TO EXTEND
 BEYOND EDGE TO FORM TEAR-TAB.
 MOUNT IS DESIGNED TO SUPPORT .20 lbs. (91g)
 MAX. WEIGHT ON A CLEAN, DRY, SMOOTH SURFACE.

| PANDUIT PART NUMBER* | MAXIMUM CABLE DIA. in. (mm) | WEIGHT lbs. (g)/100pcs |
|----------------------|--------------------------------|---------------------------|
| ACC19-A | .19 (4.8) | .17 (77) |
| ACC19-AT | .19 (4.8) | .17 (77) |

- TO APPLY ADHESIVE CORD CLIP:
1. REMOVE PROTECTIVE LINER
 2. PLACE IN DESIRED LOCATION
 3. APPLY PRESSURE TO TOP OF CORD CLIP

NOTES:

- * 1) SEE CURRENT PRICE SHEET FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE AND PART COLOR.

(DIMENSIONS IN PARENTHESES ARE METRIC)

CAD FILENAME/LAYERS

G00239GG_DC_01

PANDUIT

CORP. TINLEY PARK, ILLINOIS

ADHESIVE CORD CLIP
 ACC19-A & ACC19-AT

UNLESS OTHERWISE SPECIFIED,
 DIMENSIONAL TOLERANCES ARE:
 (.X) ± N/A (.XXX) ± N/A
 (.XX) ± .02 (.5) ANGLES ± 5°

UNLESS OTHERWISE SPECIFIED,
 ALL DIMENSIONS ARE GIVEN
 IN INCHES, THIRD ANGLE PROJECTION.

| REV | DATE | BY | CHK | DESCRIPTION | ECN | R | CUST | SUP |
|-----|---------|------|-----|---------------------------|----------|---|------|-----|
| I | 7-15-99 | CGSM | | REPLACED ISO VIEW | GB0239GG | I | | |
| R | 2-23-99 | CGSM | | RE-DRAWN FROM DWG SS-7173 | GB0239GG | R | | |

DRAWN BY
 CGSM

DATE
 2-23-99

CHK'D

MAT'L:

NYLON 6/6

SCALE
 FULL

DRAWING NO.
 GB0239GG

DWG
 SIZE
 A