

Product Description



Application range

- Insulating tubes
- For insulation of connections. Not suitable for shrinking.

Design

- Colours: black RAL 9005, white similar to RAL 9003

Approvals

- IEC 60684-3-100

Note

- 0.1 mm wall thickness = 1 kv dielectric strength

Product features

- Smooth surface



Technical Data

Info

Without fabric

Heat-resistant

Colour delivered

Black and white

Material

Soft PVC

Smooth surface

Temperature range

-10°C to +60°C

Article List

Part number	Article designation	Colour	Internal Ø x wall thickness (mm)	Material	Contents (m)
61793030	ISY 2	black	2 x 0,4	PVC	1000
61793040	ISY 3	black	3 x 0,4	PVC	750
61793050	ISY 4	black	4 x 0,5	PVC	500
61793060	ISY 5	black	5 x 0,6	PVC	500
61793070	ISY 6	black	6 x 0,6	PVC	400
61793080	ISY 7	black	7 x 0,7	PVC	500
61793090	ISY 8	black	8 x 0,7	PVC	500
61793100	ISY 9	black	9 x 0,7	PVC	400
61793110	ISY 10	black	10 x 0,7	PVC	300
61793116	ISY 10	white	10 x 0,7	PVC	300
61793119	ISY 16	black	16 x 1	PVC	150

Footnote:

Photographs are not to scale and do not represent detailed images of the respective products.