
Item no.: 2273-203
Product description: COMPACT connector for junction boxes 3-CONDUCTOR
TERMINAL BLOCKS



Produkt kann von Bild abweichen / product may differ

Packing unit 1000 10*100 pieces

RoHS compliant

pole count	3
Cross section [mm ²]	0.5 - 2.5 mm ²
Cross section [AWG]	18 - 14 AWG
Wiring method	e
Connection method	PUSH WIRE®
Number of strands	3
Measured voltage EN	450 V
Measured shock voltage	4 kV
Pollution degree	2
Current intensity EN	24 A
Weight	0 g
Color	transparent/orange
Wiring type	Side-entry
No. of connection Points	3
No. of potentials	1
Height	5.8 mm
Height	0.228 in
Width	14 mm
Width	0.551 in

Depth	16.7 mm
Depth	0.657 in
Strip length from	11 mm



Strip length to	11 mm
Strip length	0.43 in
Customs Tariff No.	85369010
Country of Origin	Deutschland

© WAGO Kontakttechnik GmbH & Co. KG

Specifications are subject to changes and errors may be expected