



**SPECIFICATION**

Braiding sleeve

Bundle range:  
 ø10mm - ø10 ~ ø20mm  
 ø22mm - ø22 ~ ø35mm  
 ø30mm - ø30 ~ ø55mm

Material: PET  
 Color: Black  
 Operating Temp. : -50°C ~ 125°C  
 Flame resistant class: VW-1

3:1 adhesive lined heat-shrink tube

Dia. for before and after shrinking:  
 ø24mm / ø8mm  
 ø40mm / ø14mm  
 ø50mm / ø16mm  
 Color: Black  
 Operating Temp.: -50°C ~ 125°C  
 Shrinking Temp.: start from 70°C,  
 full recovery at 120°C  
 Flame resistant class: VW-1

Cable Tie

Material: PA66  
 Color: Black  
 Flame resistant class: 94V-2

**Contents :**

Braiding sleeve

ø10mm x L:500mm x 2pcs  
 ø22mm x L:500mm x 2pcs  
 ø30mm x L:500mm x 1pc

3:1 adhesive lined heat-shrink tube

ø24mm x L:82mm x 3pcs  
 ø40mm x L:50mm x 3pcs  
 ø50mm x L:50mm x 2pcs

Cable Tie

100mm x 2.5mm x 20pcs

				DRAW No	SU-1003004	
DATE	REVISION	APPROVAL BY	DIMENSION	mm	MODEL No	SUBHT-01
			DRAW BY	<b>RIKKI</b>	NAME	Wire Protecting Sleeves Set
			APPROVAL BY	<i>Andy</i>		
			DATE	12-03-10		