



ITEM-NO. (ITEM-NO.)	726-321
Cross section1 (Cross section / mm²)	0.08 - 1.5
Cross section2 (Cross section / AWG)	28 - 16
Strip length (Strip length / mm)	8 - 10
Measured voltage (Measured voltage / V)	500
Measured shock voltage (Measured shock voltage / kV)	6
Pollution degree (Pollution degree)	3
Current intensity (Current intensity / A)	10
P (NO. OF POLES)	32
Height (Height / mm)	132
Width (Width / mm)	34.6
Depth (Depth / mm)	36.5
COLOR (COLOR)	dunkelgrau
WEIGHT (WEIGHT / g)	142.8