


Data sheet | Item number: 726-325

Matrix patchboard; Marking 1-32; Colors of modules: gray/white; Numbering of modules on sides 1 and 2 arranged vertically and horizontally; for 19" racks; 180° rotated; Slimline version; 32-pole



www.wago.com/726-325





Data

Electrical data

Ratings per IEC/EN 60664-1

Rated voltage (III / 3)	500 V
Rated impulse voltage (III / 3)	6 kV
Rated current	10 A
Legend (ratings)	(III / 3) ≙ Overvoltage category III / Pollution degree 3

Connection data

Connection type (1)	Side 1
Connection technology	CAGE CLAMP®
Number of connection points (connection type)	3
Actuation type	Operating tool
Connectable conductor materials	Copper Aluminum
Solid conductor	0.08 ... 1.5 mm ² / 28 ... 16 AWG
Fine-stranded conductor	0.08 ... 1.5 mm ² / 28 ... 16 AWG
Strip length	8 ... 10 mm / 0.31 ... 0.39 Inch
Connection type (2)	Side 2
Number of connection points	3
No. of poles	32
Type of wiring	Front-entry wiring

Geometrical Data

Width	34.6 mm / 1.362 inch
Height	132 mm / 5.197 inch
Depth	36.5 mm / 1.437 inch

Mechanical data

Design	slimline
Marking	Marking 1-32

Material Data

Color	dark gray
Fire load	1.795 MJ
Weight	139.906 g

Commercial data


Country of origin	DE
GTIN	4044918456081
Customs Tariff No.	85369010000

Approvals / Certificates

Country specific Approvals



Logo	Approval	Certificate name
	CSA DEKRA Certification B.V.	1101143
	KEMA/KEUR DEKRA Certification B.V.	71-100850

UL-Approvals

Logo	Approval	Certificate name
	UL UL International Germany GmbH	E45172

Compatible products

General accessories

	Item no.: 726-902 Adaptor	www.wago.com/726-902
	Item no.: 726-903 Additional module for matrix patchboards; for snap-on fixing to the lower fixing element; Additional module with contact to mounting frame	www.wago.com/726-903
	Item no.: 726-904 Additional module for matrix patchboards; for snap-on fixing to the lower fixing element; insulated;	www.wago.com/726-904



Additional module

Jumper
**Item no.: 709-107**

Wire commoning chain; insulated; 32 connections

www.wago.com/709-107

Insulation stop
**Item no.: 726-901**Insulation stop; 0.08 - 0.2 mm² "s" (0.14 mm² "f-st"); 4 x 3 pieces/stripwww.wago.com/726-901**Item no.: 726-906**Insulation stop; 0.25 mm² "s"; 0.14 - 0.25 mm² "f-st"; 4 x 3 pieces/stripwww.wago.com/726-906**Item no.: 726-907**Insulation stop; 0.25 - 0.5 mm² "s+f-st"; 4 x 3 pieces/stripwww.wago.com/726-907

Marking accessories
**Item no.: 209-185**

Adaptor

www.wago.com/209-185**Item no.: 209-500/209-035**

WSB marking card; as card; MARKED; X (100x); not stretchable; Horizontal marking; snap-on type

www.wago.com/209-500/209-035**Item no.: 209-501**

WSB marking card; as card; not stretchable; plain; snap-on type

www.wago.com/209-501**Item no.: 209-501/000-002**

WSB marking card; as card; not stretchable; plain; snap-on type

www.wago.com/209-501/000-002**Item no.: 209-501/000-005**

WSB marking card; as card; not stretchable; plain; snap-on type

www.wago.com/209-501/000-005**Item no.: 209-501/000-006**

WSB marking card; as card; not stretchable; plain; snap-on type

www.wago.com/209-501/000-006**Item no.: 209-501/000-007**

WSB marking card; as card; not stretchable; plain; snap-on type

www.wago.com/209-501/000-007**Item no.: 209-501/000-012**

WSB marking card; as card; not stretchable; plain; snap-on type

www.wago.com/209-501/000-012**Item no.: 209-501/000-017**

WSB marking card; as card; not stretchable; plain; snap-on type

www.wago.com/209-501/000-017**Item no.: 209-501/000-023**

WSB marking card; as card; not stretchable; plain; snap-on type

www.wago.com/209-501/000-023



Item no.: 209-501/000-024
WSB marking card; as card; not stretchable; plain; snap-on type

www.wago.com/209-501/000-024



Item no.: 209-502
WSB marking card; as card; MARKED; 1 ... 10 (10x); not stretchable; Horizontal marking; snap-on type

www.wago.com/209-502



Item no.: 209-566
WSB marking card; as card; MARKED; 1 ... 50 (2x); not stretchable; Horizontal marking; snap-on type

www.wago.com/209-566



Item no.: 210-612
Marking strips; for self-marking; plain; Self-adhesive

www.wago.com/210-612



Item no.: 726-905
Adaptor

www.wago.com/726-905

tools



Item no.: 210-719
Operating tool with partially insulated shaft; Type 1, blade (2.5 x 0.4) mm

www.wago.com/210-719

check



Item no.: 210-137
Test plug; 2.3 mm Ø; with 500 mm cable

www.wago.com/210-137

ferrule



Item no.: 216-104
Ferrule; Sleeve for 1.5 mm² / AWG 16; uninsulated; electro-tin plated

www.wago.com/216-104



Item no.: 216-123
Ferrule; Sleeve for 1 mm² / AWG 18; uninsulated; electro-tin plated

www.wago.com/216-123



Item no.: 216-202
Ferrule; Sleeve for 0.75 mm² / AWG 20; insulated; electro-tin plated

www.wago.com/216-202



Item no.: 216-204
Ferrule; Sleeve for 1.5 mm² / AWG 16; insulated; electro-tin plated

www.wago.com/216-204

Downloads

Documentation

Bid Text

726-325

Oct 18, 2017

DOC
26.1 kB

Download



Subject to changes.

WAGO Kontakttechnik GmbH & Co. KG
Hansastr. 27
32423 Minden
Phone: +49571 887-0 | Fax: +49571 887-169
Email: info.de@wago.com | Web: www.wago.com

Do you have any questions about our products?
We are always happy to take your call at +49 (571) 887-44222.