



<b>ITEM-NO. (ITEM-NO.)</b>	726-441
<b>Cross section1 (Cross section / mm<sup>2</sup>)</b>	0.08 - 1.5
<b>Cross section2 (Cross section / AWG)</b>	28 - 16
<b>Strip length (Strip length / mm)</b>	8 - 10
<b>Measured voltage (Measured voltage / V)</b>	500
<b>Measured shock voltage (Measured shock voltage / kV)</b>	6
<b>Pollution degree (Pollution degree)</b>	3
<b>Current intensity (Current intensity / A)</b>	10
<b>P (NO. OF POLES)</b>	48
<b>Height (Height / mm)</b>	132
<b>Width (Width / mm)</b>	65.3
<b>Depth (Depth / mm)</b>	36.5
<b>COLOR (COLOR)</b>	dunkelgrau
<b>WEIGHT (WEIGHT / g)</b>	250.542