



| | |
|---|------------|
| ITEM-NO. (ITEM-NO.) | 726-721 |
| Cross section1 (Cross section / mm²) | 0.08 - 1.5 |
| Cross section2 (Cross section / AWG) | 28 - 16 |
| Strip length (Strip length / mm) | 8 - 10 |
| Measured voltage (Measured voltage / V) | 500 |
| Measured shock voltage (Measured shock voltage / kV) | 6 |
| Pollution degree (Pollution degree) | 3 |
| Current intensity (Current intensity / A) | 10 |
| P (NO. OF POLES) | 80 |
| Height (Height / mm) | 132 |
| Width (Width / mm) | 107.9 |
| Depth (Depth / mm) | 36.5 |
| COLOR (COLOR) | dunkelgrau |
| WEIGHT (WEIGHT / g) | 420.75 |