



SPECIFICATION

Normal flash energy	8WS
Design anode voltage	330V
Max. anode voltage	350V
Min. anode voltage	180V
Min. trigger voltage	3KV
Dimensions A	26mm MAX
Dimensions B	22±1mm
Dimensions C	14±1mm
Dimensions D	∅2.5±0.1mm
Flash rate at normal energy	15Sec.
Life	1000 Flashes

DESIGNED BY



TYPE NO.

FT-2522

CHECKED



NAME

XENON FLASH TUBE