





**8-LEVEL TERMINAL BLOCK FOR  
MATRIX PATCHING CENTRE  
MARKING WITHOUT LOCKING CLIPS  
727-120**

|   |                 |
|---|-----------------|
| <b>ITEM-NO. (ITEM-NO.)</b>                                  | 727-124/002-000 |
| <b>Cross section1 (Cross section / mm<sup>2</sup>)</b>      | 0.08 - 1.5      |
| <b>Cross section2 (Cross section / AWG)</b>                 | 28 - 16         |
| <b>Strip length (Strip length / mm)</b>                     | 8 - 10          |
| <b>Measured voltage (Measured voltage / V)</b>              | 250             |
| <b>Measured shock voltage (Measured shock voltage / kV)</b> | 4               |
| <b>Pollution degree (Pollution degree)</b>                  | 3               |
| <b>Current intensity (Current intensity / A)</b>            | 10              |
| <b>Height (Height / mm)</b>                                 | 58.5            |
| <b>Width (Width / mm)</b>                                   | 7.62            |
| <b>Depth (Depth / mm)</b>                                   | 226             |
| <b>No. of connection Points (No. of connection Points)</b>  | 32              |
| <b>No. of potentials (No. of potentials)</b>                | 8               |
| <b>COLOR (COLOR)</b>  | blau            |
| <b>WEIGHT (WEIGHT / g)</b>                                  | 75              |