



**8-LEVEL SAME POTENTIAL
TERMINAL BLOCK CENTRE
MARKING WITHOUT LOCKING CLIPS
727-126**

ITEM-NO. (ITEM-NO.)	727-128/002-000
Cross section1 (Cross section / mm²)	0.08 - 1.5
Cross section2 (Cross section / AWG)	28 - 16
Strip length (Strip length / mm)	8 - 10
Measured voltage (Measured voltage / V)	250
Measured shock voltage (Measured shock voltage / kV)	4
Pollution degree (Pollution degree)	3
Current intensity (Current intensity / A)	18
Height (Height / mm)	58.5
Width (Width / mm)	7.62
Depth (Depth / mm)	226
No. of connection Points (No. of connection Points)	32
No. of potentials (No. of potentials)	8
COLOR (COLOR)	lichtgrau
WEIGHT (WEIGHT / g)	58.687
RGB (RGB)	0.82,0.82,0.82,0