





**4-LEVEL TERMINAL BLOCK FOR  
MATRIX PATCHING CENTRE  
MARKING WITH LOCKING CLIPS  
727-219**

|   |                     |
|---|---------------------|
| <b>ITEM-NO. (ITEM-NO.)</b>                                  | 727-221/024-000     |
| <b>Cross section1 (Cross section / mm<sup>2</sup>)</b>      | 0.08 - 1.5          |
| <b>Cross section2 (Cross section / AWG)</b>                 | 28 - 16             |
| <b>Strip length (Strip length / mm)</b>                     | 8 - 10              |
| <b>Measured voltage (Measured voltage / V)</b>              | 250                 |
| <b>Measured shock voltage (Measured shock voltage / kV)</b> | 4                   |
| <b>Pollution degree (Pollution degree)</b>                  | 3                   |
| <b>Current intensity (Current intensity / A)</b>            | 12                  |
| <b>Height (Height / mm)</b>                                 | 62                  |
| <b>Width (Width / mm)</b>                                   | 7.62                |
| <b>Depth (Depth / mm)</b>                                   | 126                 |
| <b>No. of connection Points (No. of connection Points)</b>  | 16                  |
| <b>No. of potentials (No. of potentials)</b>                | 4                   |
| <b>COLOR (COLOR)</b>  | weiß                |
| <b>WEIGHT (WEIGHT / g)</b>                                  | 33.01               |
| <b>Comment (Comment)</b>                                    | d-c-b-a - - a-b-c-d |