





**4-LEVEL SAME POTENTIAL
TERMINAL BLOCK CENTRE
MARKING WITHOUT LOCKING CLIPS
727-226**

PDF DATASHEET

© 1992 - 2011 | CADENAS GmbH

ITEM-NO. (ITEM-NO.)	727-226/023-000
Cross section1 (Cross section / mm²)	0.08 - 1.5
Cross section2 (Cross section / AWG)	28 - 16
Strip length (Strip length / mm)	8 - 10
Measured voltage (Measured voltage / V)	250
Measured shock voltage (Measured shock voltage / kV)	4
Pollution degree (Pollution degree)	3
Current intensity (Current intensity / A)	18
Height (Height / mm)	44.5
Width (Width / mm)	7.62
Depth (Depth / mm)	126
No. of connection Points (No. of connection Points)	16
No. of potentials (No. of potentials)	4
COLOR (COLOR)	orange
WEIGHT (WEIGHT / g)	29.625
Comment (Comment)	3-2-1-0 - - 0-1-2-3