



| | |
|---|---------------|
| ITEM-NO. (ITEM-NO.) | 727-228 |
| Cross section1 (Cross section / mm²) | 0.08 - 1.5 |
| Cross section2 (Cross section / AWG) | 28 - 16 |
| Strip length (Strip length / mm) | 8 - 10 |
| Measured voltage (Measured voltage / V) | 250 |
| Measured shock voltage (Measured shock voltage / kV) | 4 |
| Pollution degree (Pollution degree) | 3 |
| Current intensity (Current intensity / A) | 18 |
| Height (Height / mm) | 44.5 |
| Width (Width / mm) | 7.62 |
| Depth (Depth / mm) | 126 |
| No. of connection Points (No. of connection Points) | 16 |
| No. of potentials (No. of potentials) | 1 |
| COLOR (COLOR) | lichtgrau |
| WEIGHT (WEIGHT / g) | 29.625 |
| Comment (Comment) | ohne Aufdruck |