





**4-LEVEL SAME POTENTIAL  
TERMINAL BLOCK CENTRE  
MARKING WITHOUT LOCKING CLIPS  
727-226**

<b>ITEM-NO. (ITEM-NO.)</b>	727-228/022-000
<b>Cross section1 (Cross section / mm<sup>2</sup>)</b>	0.08 - 1.5
<b>Cross section2 (Cross section / AWG)</b>	28 - 16
<b>Strip length (Strip length / mm)</b>	8 - 10
<b>Measured voltage (Measured voltage / V)</b>	250
<b>Measured shock voltage (Measured shock voltage / kV)</b>	4
<b>Pollution degree (Pollution degree)</b>	3
<b>Current intensity (Current intensity / A)</b>	18
<b>Height (Height / mm)</b>	44.5
<b>Width (Width / mm)</b>	7.62
<b>Depth (Depth / mm)</b>	126
<b>No. of connection Points (No. of connection Points)</b>	16
<b>No. of potentials (No. of potentials)</b>	4
<b>COLOR (COLOR)</b>	lichtgrau
<b>WEIGHT (WEIGHT / g)</b>	29.625
<b>Comment (Comment)</b>	a-b-c-d - - d-c-b-a