



ITEM-NO. (ITEM-NO.)	732-102/026-000
Cross section1 (Cross section / mm²)	0.08 - 2.5
Cross section2 (Cross section / AWG)	28 - 12
Strip length (Strip length / mm)	8 - 9
Measured voltage (Measured voltage / V)	630
Measured shock voltage (Measured shock voltage / kV)	6
Pollution degree (Pollution degree)	2
Current intensity (Current intensity / A)	14
RM (PIN SPACING / mm)	7.5
P (NO. OF POLES)	2
Height (Height / mm)	23.9
Width (Width / mm)	14.9
Depth (Depth / mm)	22.75
No. of connection Points (No. of connection Points)	2
No. of potentials (No. of potentials)	2
COLOR (COLOR)	grau
Comment (Comment)	L = (No. of poles - 1) x Pin Spacing + 5 mm + 1,5 mm + 0,9 mm