





Angled female plug pin spacing 7.62 mm / 0.3 in with codig fingers
732-122/026-000 TO 732-136/026-000

ITEM-NO. (ITEM-NO.)	732-123/026-000
Cross section1 (Cross section / mm²)	0.08 - 2.5
Cross section2 (Cross section / AWG)	28 - 12
Strip length (Strip length / mm)	8 - 9
Measured voltage (Measured voltage / V)	630
Measured shock voltage (Measured shock voltage / kV)	6
Pollution degree (Pollution degree)	2
Current intensity (Current intensity / A)	14
RM (PIN SPACING / mm)	7.62
P (NO. OF POLES)	3
Height (Height / mm)	23.9
Width (Width / mm)	22.72
Depth (Depth / mm)	22.75
No. of connection Points (No. of connection Points)	3
No. of potentials (No. of potentials)	3
COLOR (COLOR)	orange
Comment (Comment)	L = (No. of poles - 1) x Pin Spacing + 5 mm + 1,5 mm + 0,9 mm