




SPECIFICATION

Parts No: C-E3E-1.2

Customer : _____
 Description : _____
 Specification : 8X8X16
 Parts No : C-E3E-1.2
 Remark : _____

REV : 01
 DATE : 2016.07.08

一、Mechanical :



二. Electrical Requirement		三. Test Instruments		
1、Inductance		1、Inductance	TH2811 Type LCR Digital bridge	
PIN: 1-2	15+/-4uH	2、DC Resistance	TH2811 Type LCR Digital bridge	
PIN: 2-3	25+/-5mH	3、OutPut	Tektronix TDS1012	
2、DC Resistance		4、INSULATION	MS2670B Type Voltage tester	
PIN: 1-2	0.35Ω (MAX)		PRIMARY	SECONDARY
PIN: 2-3	140Ω+/-20%	PRIMARY VOLTAGE, Uzp	200V	11KVp-p
Turns ratio	43:1 0.23/34T 0.05/1420T	PRIMARY CAPACITANCE	0.047uF
4、INSULATION Pressure	20KV (MIN)	SECONDARY VOLTAGE, Uzsec	

Remark

Approved By	Checked By	Quality Protection	Drawn By