



**HEADER STRAIGHT SOLDER PIN, 1X1  
MM / 0.039X 0.039 IN PIN SPACING 3.5  
MM / 0.138 IN 100% PROTECTED  
AGAINST MISMATING  
734-132/105-604 TO 734-144/105-604**

<b>ITEM-NO. (ITEM-NO.)</b>	734-132/105-604
<b>Measured voltage (Measured voltage / V)</b>	160
<b>Measured shock voltage (Measured shock voltage / kV)</b>	2.5
<b>Pollution degree (Pollution degree)</b>	2
<b>Current intensity (Current intensity / A)</b>	10
<b>RM (PIN SPACING / mm)</b>	3.5
<b>P (NO. OF POLES)</b>	2
<b>Height (Height / mm)</b>	10.3
<b>Width (Width / mm)</b>	9.4
<b>Depth (Depth / mm)</b>	8.5
<b>COLOR (COLOR)</b>	schwarz
<b>Comment (Comment)</b>	$L = (\text{No. of poles} - 1) \times \text{Pin Spacing} + 5,9 \text{ mm}$
<b>Dimensions (Dimensions)</b>	1,4 +0,1 mm