



**HEADER STRAIGHT SOLDER PIN, 1X1
MM / 0.039X 0.039 IN PIN SPACING 3.5
MM / 0.138 IN 100% PROTECTED
AGAINST MISMATING
734-132 TO 734-154**

| | |
|---|--|
| ITEM-NO. (ITEM-NO.) | 734-146 |
| Measured voltage (Measured voltage / V) | 160 |
| Measured shock voltage (Measured shock voltage / kV) | 2.5 |
| Pollution degree (Pollution degree) | 2 |
| Current intensity (Current intensity / A) | 10 |
| RM (PIN SPACING / mm) | 3.5 |
| P (NO. OF POLES) | 16 |
| Height (Height / mm) | 10.3 |
| Width (Width / mm) | 58.4 |
| Depth (Depth / mm) | 8.5 |
| COLOR (COLOR) | lichtgrau |
| Comment (Comment) | $L = (\text{No. of poles} - 1) \times \text{Pin Spacing} + 5,9 \text{ mm}$ |
| Dimensions (Dimensions) | 1,4 +0,1 mm |