



**HEADER RIGHT ANGLE SOLDER PIN,
1 X 1 MM / 0.039 X 0.039 IN PIN
SPACING 3.5 MM / 0.138 IN 100%
PROTECTED AGAINST MISMATING
WITH THREADED FLANGES MATING
734-162/108-000 TO 734-184/108-000**

ITEM-NO. (ITEM-NO.)	734-166/108-000
Measured voltage (Measured voltage / V)	160
Measured shock voltage (Measured shock voltage / kV)	2.5
Pollution degree (Pollution degree)	2
Current intensity (Current intensity / A)	10
RM (PIN SPACING / mm)	3.5
P (NO. OF POLES)	6
Height (Height / mm)	8.5
Width (Width / mm)	23.4
Depth (Depth / mm)	10.3
COLOR (COLOR)	lichtgrau
Comment (Comment)	L = (No. of poles - 1) x Pin Spacing + 5,9 mm
Dimensions (Dimensions)	1,4 +0,1 mm