



**HEADER RIGHT ANGLE SOLDER PIN,
1 X 1 MM / 0.039 X 0.039 IN PIN
SPACING 3.5 MM / 0.138 IN 100%
PROTECTED AGAINST MISMATING
734-162 TO 734-184**

ITEM-NO. (ITEM-NO.)	734-170
Measured voltage (Measured voltage / V)	160
Measured shock voltage (Measured shock voltage / kV)	2.5
Pollution degree (Pollution degree)	2
Current intensity (Current intensity / A)	10
RM (PIN SPACING / mm)	3.5
P (NO. OF POLES)	10
Height (Height / mm)	8.5
Width (Width / mm)	37.4
Depth (Depth / mm)	10.3
COLOR (COLOR)	lichtgrau
Comment (Comment)	$L = (\text{No. of poles} - 1) \times \text{Pin Spacing} + 5,9 \text{ mm}$
Dimensions (Dimensions)	1,4 +0,1 mm