



**HEADER RIGHT ANGLE SOLDER PIN,  
1 X 1 MM / 0.039 X 0.039 IN PIN  
SPACING 3.5 MM / 0.138 IN 100%  
PROTECTED AGAINST MISMATING  
734-162 TO 734-184**

|   |   |
|---|---|
| <b>ITEM-NO. (ITEM-NO.)</b>                                  | 734-173                                       |
| <b>Measured voltage (Measured voltage / V)</b>              | 160   |
| <b>Measured shock voltage (Measured shock voltage / kV)</b> | 2.5   |
| <b>Pollution degree (Pollution degree)</b>                  | 2   |
| <b>Current intensity (Current intensity / A)</b>            | 10  |
| <b>RM (PIN SPACING / mm)</b>                                | 3.5   |
| <b>P (NO. OF POLES)</b>                                     | 13  |
| <b>Height (Height / mm)</b>                                 | 8.5   |
| <b>Width (Width / mm)</b>                                   | 47.9  |
| <b>Depth (Depth / mm)</b>                                   | 10.3  |
| <b>COLOR (COLOR)</b>  | lichtgrau                                     |
| <b>Comment (Comment)</b>                                    | L = (No. of poles - 1) x Pin Spacing + 5,9 mm |
| <b>Dimensions (Dimensions)</b>                              | 1,4 +0,1 mm                                   |