



ITEM-NO. (ITEM-NO.)	734-210
Cross section1 (Cross section / mm²)	0.08 - 1.5
Cross section2 (Cross section / AWG)	28 - 14
Strip length (Strip length / mm)	7
Measured voltage (Measured voltage / V)	160
Measured shock voltage (Measured shock voltage / kV)	2.5
Pollution degree (Pollution degree)	2
Current intensity (Current intensity / A)	10
RM (PIN SPACING / mm)	3.81
P (NO. OF POLES)	10
Height (Height / mm)	13.4
Width (Width / mm)	40.3
Depth (Depth / mm)	18.6
No. of connection Points (No. of connection Points)	10
No. of potentials (No. of potentials)	10
COLOR (COLOR)	orange
WEIGHT (WEIGHT / g)	8.276
Comment (Comment)	L = (No. of poles x Pin Spacing) + 2,2 mm