



**HEADER RIGHT ANGLE SOLDER PIN,
1 X 1 MM / 0.039 X 0.039 IN PIN
SPACING 3.81 MM / 0.15 IN 100%
PROTECTED AGAINST MISMATING
734-262 TO 734-280**

ITEM-NO. (ITEM-NO.)	734-269
Measured voltage (Measured voltage / V)	160
Measured shock voltage (Measured shock voltage / kV)	2.5
Pollution degree (Pollution degree)	2
Current intensity (Current intensity / A)	10
RM (PIN SPACING / mm)	3.81
P (NO. OF POLES)	9
Height (Height / mm)	8.5
Width (Width / mm)	36.38
Depth (Depth / mm)	10.3
COLOR (COLOR)	orange
WEIGHT (WEIGHT / g)	2.566
Comment (Comment)	L = (No. of poles - 1) x Pin Spacing + 5,9 mm
Dimensions (Dimensions)	1,4 +0,1 mm