





**MALE CONNECTOR WITH SNAP-IN
MOUNTING FOOT PIN SPACING 3.5
MM / 0.138 IN**
734-302/018-000 TO 734-324/018-000

| | |
|---|---|
| ITEM-NO. (ITEM-NO.) | 734-306/018-000 |
| Cross section1 (Cross section / mm²) | 0.08 - 1.5 |
| Cross section2 (Cross section / AWG) | 28 - 14 |
| Strip length (Strip length / mm) | 6 - 7 |
| Measured voltage (Measured voltage / V) | 160 |
| Measured shock voltage (Measured shock voltage / kV) | 2.5 |
| Pollution degree (Pollution degree) | 2 |
| Current intensity (Current intensity / A) | 10 |
| RM (PIN SPACING / mm) | 3.5 |
| P (NO. OF POLES) | 6 |
| Height (Height / mm) | 13.4 |
| Width (Width / mm) | 23.4 |
| Depth (Depth / mm) | 22.3 |
| No. of connection Points (No. of connection Points) | 6 |
| No. of potentials (No. of potentials) | 6 |
| COLOR (COLOR) | lichtgrau |
| Comment (Comment) | L = (No. of poles - 1) x Pin Spacing + 5,9 mm + 0,45 mm L1 = L - 0,45 mm |