



**MALE CONNECTOR WITH FIXING
FLANGE PIN SPACING 3.81 MM / 0.15
IN 100% PROTECTED AGAINST
MISMATING**

734-332/019-000 TO 734-350/019-000

ITEM-NO. (ITEM-NO.)	734-339/019-000
Cross section1 (Cross section / mm²)	0.08 - 1.5
Cross section2 (Cross section / AWG)	28 - 14
Strip length (Strip length / mm)	6 - 7
Measured voltage (Measured voltage / V)	160
Measured shock voltage (Measured shock voltage / kV)	2.5
Pollution degree (Pollution degree)	2
Current intensity (Current intensity / A)	10
RM (PIN SPACING / mm)	3.81
P (NO. OF POLES)	9
Height (Height / mm)	13.4
Width (Width / mm)	49.09
Depth (Depth / mm)	22.3
No. of connection Points (No. of connection Points)	9
No. of potentials (No. of potentials)	9
COLOR (COLOR)	orange
Comment (Comment)	L = (No. of poles x Pin Spacing) + 14,8 mm L1 = (No. of poles x Pin Spacing) + 8,8 mm L2 = (No. of poles x Pin Spacing) L3 = (No. of poles - 1) + 5,9 mm