



**Double deck headers right angle
solder pin, 1 x 1 mm / 0.039 x 0.039 in
pin spacing 3.5 mm / 0.138 in 100%
protected against mismatching without
support mating
734-402 TO 734-412**

| | |
|---|--|
| ITEM-NO. (ITEM-NO.) | 734-403 |
| Measured voltage (Measured voltage / V) | 160 |
| Measured shock voltage (Measured shock voltage / kV) | 2.5 |
| Pollution degree (Pollution degree) | 2 |
| Current intensity (Current intensity / A) | 10 |
| RM (PIN SPACING / mm) | 3.5 |
| P (NO. OF POLES) | 3 |
| Height (Height / mm) | 23 |
| Width (Width / mm) | 12.9 |
| Depth (Depth / mm) | 16.8 |
| COLOR (COLOR) | lichtgrau |
| Comment (Comment) | L1 = (No. of poles/2 - 1) x Pin Spacing + 5,9 mm |
| Dimensions (Dimensions) | 1.4 +0.1 mm |