





**DOUBLE DECK HEADERS RIGHT  
ANGLE SOLDER PIN, 1 X 1 MM / 0.039  
X 0.039 IN PIN SPACING 3.5 MM / 0.  
138 IN 100% PROTECTED AGAINST  
MISMATING**  
734-402/001-000 TO 734-412/001-000

**PDF DATASHEET**

© 1992 - 2011 CADENAS GmbH

<b>ITEM-NO. (ITEM-NO.)</b>	734-410/001-000
<b>Measured voltage (Measured voltage / V)</b>	160
<b>Measured shock voltage (Measured shock voltage / kV)</b>	2.5
<b>Pollution degree (Pollution degree)</b>	2
<b>Current intensity (Current intensity / A)</b>	10
<b>RM (PIN SPACING / mm)</b>	3.5
<b>P (NO. OF POLES)</b>	10
<b>Height (Height / mm)</b>	23
<b>Width (Width / mm)</b>	37.4
<b>Depth (Depth / mm)</b>	16.8
<b>COLOR (COLOR)</b>	lichtgrau
<b>WEIGHT (WEIGHT / g)</b>	10.9
<b>Comment (Comment)</b>	L1 = (No. of poles/2 - 1) x Pin Spacing + 5,9 mm
<b>Dimensions (Dimensions)</b>	1,4 +0,1 mm