



**DOUBLE DECK HEADERS RIGHT
ANGLE SOLDER PIN, 1 X 1 MM / 0.039
X 0.039 IN PIN SPACING 3.5 MM / 0.
138 IN 100% PROTECTED AGAINST
MISMATING**
734-402/001-000 TO 734-412/001-000

ITEM-NO. (ITEM-NO.)	734-412/001-000
Measured voltage (Measured voltage / V)	160
Measured shock voltage (Measured shock voltage / kV)	2.5
Pollution degree (Pollution degree)	2
Current intensity (Current intensity / A)	10
RM (PIN SPACING / mm)	3.5
P (NO. OF POLES)	12
Height (Height / mm)	23
Width (Width / mm)	44.4
Depth (Depth / mm)	16.8
COLOR (COLOR)	lichtgrau
WEIGHT (WEIGHT / g)	13.004
Comment (Comment)	L1 = (No. of poles/2 - 1) x Pin Spacing + 5,9 mm
Dimensions (Dimensions)	1,4 +0,1 mm