



**Double deck headers right angle
solder pin, 1 x 1 mm / 0.039 x 0.039 in
pin spacing 3.81 mm / 0.15 in 100%
protected against mismatching without
support mating
734-432 TO 734-442**

ITEM-NO. (ITEM-NO.)	734-432
Measured voltage (Measured voltage / V)	160
Measured shock voltage (Measured shock voltage / kV)	2.5
Pollution degree (Pollution degree)	2
Current intensity (Current intensity / A)	10
RM (PIN SPACING / mm)	3.81
P (NO. OF POLES)	2
Height (Height / mm)	23
Width (Width / mm)	9.71
Depth (Depth / mm)	16.8
COLOR (COLOR)	orange
Comment (Comment)	L1 = No. Of poles / 2 - 1) x Pin Spacing + 5.9 mm
Dimensions (Dimensions)	1.4 + 0.1 mm