



**Double deck headers right angle  
solder pin, 1 x 1 mm / 0.039 x 0.039 in  
pin spacing 3.81 mm / 0.15 in 100%  
protected against mismatching with  
support mating**  
734-432/001-000 TO 734-442/001-000

|   |   |
|---|---|
| <b>ITEM-NO. (ITEM-NO.)</b>                                  | 734-435/001-000                                   |
| <b>Measured voltage (Measured voltage / V)</b>              | 160   |
| <b>Measured shock voltage (Measured shock voltage / kV)</b> | 2.5   |
| <b>Pollution degree (Pollution degree)</b>                  | 2   |
| <b>Current intensity (Current intensity / A)</b>            | 10  |
| <b>RM (PIN SPACING / mm)</b>                                | 3.81  |
| <b>P (NO. OF POLES)</b>                                     | 5   |
| <b>Height (Height / mm)</b>                                 | 23  |
| <b>Width (Width / mm)</b>                                   | 21.14   |
| <b>Depth (Depth / mm)</b>                                   | 16.8  |
| <b>COLOR (COLOR)</b>  | orange  |
| <b>Comment (Comment)</b>                                    | L1 = No. Of poles / 2 - 1) x Pin Spacing + 5.9 mm |
| <b>Dimensions (Dimensions)</b>                              | 1.4 + 0.1 mm                                      |